



FOCAL LENGTH (EFL): 75 ± 0,75
 BACK FOCAL LENGTH (BFL): 71,96

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	34,385±0,034 CX	GLASS FUSED SILICA 458/678	R	∞ PL
Øe	24		Øe	24
3/	2 (0,2) λ=632,8 nm		3/	2 (0,2) λ=632,8 nm
4/	-		4/	2,18'
5/	20 - 10 (MIL-PRF-13830B)		5/	20 - 10 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT SCALE: NONE λ = 587,6nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE 25mm Diameter x 75mm FL, 532nm Coated, Laser Grade PCX Lens

DWG NO 67965

SHEET SIZE A4 SHEET 1 OF 1