



FOCAL LENGTH (EFL):  $5 \pm 0,05$   
 BACK FOCAL LENGTH (BFL): 4,57

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$4,251 \pm 0,004$ CX	GLASS N-LaSF9 850/322	R	$\infty$ PL
$\text{Øe}$	2		$\text{Øe}$	2
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	52,94'
5/	20 - 10 (MIL-PRF-13830B)		5/	20 - 10 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT  
 SCALE: NONE  
 $\lambda = 587,6$  nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

**EO**® Edmund Optics®

TITLE 2,5mm Dia, x 5,0mm FL, Uncoated, Plano-Convex Lens

DWG NO 48644

SHEET SIZE A4 SHEET 1 OF 1