

FOCAL LENGTH (EFL): $6 \pm 0,06$
 BACK FOCAL LENGTH (BFL): 4,38

1 AR COATING: VIS 0°
 $R(\text{AVG}) \leq 0,4\%$ FROM 425-675nm @ 0° AOI

| LEFT SURFACE | | MATERIAL | RIGHT SURFACE | |
|--------------|----------------------------|----------------------------|---------------|----------------------------|
| R | 4,76±0,005 CX | GLASS FUSED SILICA 458/678 | R | 4,76±0,005 CX |
| Øe | 5,4 | | Øe | 5,4 |
| 3/ | 3 (0,5) $\lambda=632,8$ nm | | 3/ | 3 (0,5) $\lambda=632,8$ nm |
| 4/ | - | | 4/ | 6,55' |
| 5/ | 40 - 20 (MIL-PRF-13830B) | | 5/ | 40 - 20 (MIL-PRF-13830B) |
| 6/ | - | | 6/ | - |

PROTECTIVE CHAMFERS AS NEEDED


ROHS: COMPLIANT
 SCALE: NONE $\lambda = 587,6$ nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

EO® Edmund Optics®

TITLE 6mm Dia, x 6mm FL, VIS 0 Coated, UV Double-Convex Lens

DWG NO 49262

SHEET SIZE A4 SHEET 1 OF 1