



FOCAL LENGTH (EFL):  $10 \pm 0,1$   
 BACK FOCAL LENGTH (BFL):  $9,31$

1 AR COATING: VIS-EXT  
 $R(AVG) \leq 0,5\%$  FROM 350-700nm @  $0^\circ$  AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$9,98 \pm 0,01$ CX	GLASS N-BK7 517/642	R	$9,98 \pm 0,01$ CX
Øe	4,5		Øe	4,5
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	5,8'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT    SCALE: NONE     $\lambda = 587,6$ nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

**EO**® Edmund Optics®

TITLE 5mm Dia, x 10mm FL, VIS-EXT Coated, Double-Convex Lens

DWG NO 89125

SHEET SIZE A4    SHEET 1 OF 1