

SURFACE: INR
 IDR: 0.000 MM
SPOT DIAGRAM

47639INK
 TUE DEC 16 2008 UNITS ARE μm .
 FIELD : :
 RMS RADIUS : 11.362
 SED RADIUS : 31.670
 SCALE BAR : 100



REFERENCE : CHIEF RAY

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

47639INK
 TUE DEC 16 2008
 MAXIMUM FOCAL SHIFT RANGE: 135.5884 μm
 DIFFRACTION LIMITED RANGE: 21.144 μm
 PUPIL ZONE: 0.0000

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

CHROMATIC FOCAL SHIFT



TRANSVERSE RAY FAN PLOT

47639INK
 TUE DEC 16 2008
 MAXIMUM SCALE: $\pm 100.000 \mu\text{m}$.
 0.486 0.588 0.656

SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

47639INK
 TUE DEC 16 2008
 DATA FOR 0.4250 TO 0.6750 μm .
 SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

POLYCHROMATIC DIFFRACTION MTF